

ISO cylinder DSNU-20-320-PPV-A

Part number: 34720

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Stroke	320 mm
Piston diameter	20 mm
Piston rod thread	M8
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 6432
Piston-rod end	Male thread
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Symbol	00991235
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.2 J
Cushioning length	15 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	158.3 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	188.5 N
Moving mass for 0 mm stroke	44 g
Additional moving mass per 10 mm stroke	4 g
Basic weight for 0 mm stroke	186.8 g
Additional weight per 10 mm stroke	7.2 g
Type of mounting	With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy Colourless anodised

Feature	Value
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel