

Branching module MS4-FRM

Part number: 527703

FESTO



 General operating condition

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Mounting position	Any
Design	Branching module
Symbol	00991510
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/4 Prepared for G1/8 With pressure sensor With pressure gauge
Operating pressure	0 bar ... 14 bar
Standard nominal flow rate in main flow direction 1->2	1200 l/min ... 4600 l/min
Standard nominal flow rate, outlet upwards	500 l/min ... 1600 l/min
Standard nominal flow rate, outlet downwards	500 l/min ... 1700 l/min
Approval	c UL us - Recognised (Oil)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Explosion protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T6 Gb X
Explosion ignition protection type for dust	Ex h IIIC T60°C Db X
Explosion ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Suitable for use with food	See supplementary material information
Media temperature	-10 °C ... 60 °C

Feature	Value
Ambient temperature	-10 °C ... 60 °C
Product weight	165 g
Note on materials	RoHS compliant
Material housing	Die-cast aluminium