


# Standards-based cylinder DSNU-12- -F1A-

Part number: 8149444



 General operating condition

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	1 mm ... 200 mm
Piston diameter	12 mm
Piston rod thread	M6
Cushioning	Elastic cushioning rings/plates at both ends Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 6432
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Symbol	00991217
Variants	Advancing stroke adjustment Weld spatter protection Custom thread on the piston rod Piston rod with external hexagon Low friction for balancer applications Swivelling rod eye mounting on the end cap Low friction
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.07 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	50.9 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	67.9 N
Moving mass for 0 mm stroke	18.5 g
Additional moving mass per 10 mm stroke	2 g
Basic weight for 0 mm stroke	75 g
Additional weight per 10 mm stroke	4 g

<b>Feature</b>	<b>Value</b>
Type of mounting	With accessories
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Anodised wrought aluminium alloy
Material seals	TPE-U(PU)
Material piston rod	High-alloy stainless steel
Material cylinder barrel	High-alloy stainless steel