



Safety Data Sheet according to (EC) No 1907/2006 - ISO 11014-1

Page 1 of 5

Loctite 243

sds no. : 316211
V002.0

Revision: 20.05.2010
printing date: 11.10.2010

1. Identification of the substance/preparation and of the company/undertaking

Trade name:

Loctite 243

Intended use:

Adhesive

Company name:

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933

Fax-no.: +44 1606 863762

E-mail address of person responsible for Safety Data Sheet:

ua-productsafety.uk@uk.henkel.com

Emergency information:

24 Hours Emergency Tel: +44 (0)1442 278497

2. Hazards identification

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

3. Composition / information on ingredients

General chemical description:

Anaerobic adhesive

Declaration of ingredients according to (EC) No 1907/2006:

Hazardous components CAS-No.	EINECS ELINCS	content	Classification
2,4,6-Triallyloxy-s-triazine 101-37-1	202-936-7	> 5 - < 10 %	Xn - Harmful; R22 N - Dangerous for the environment; R51/53
Cumene hydroperoxide 80-15-9	201-254-7	> 0,1 - < 0,9 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 O - Oxidizing; R7 C - Corrosive; R34 N - Dangerous for the environment; R51, R53
Cumene 98-82-8	202-704-5	> 0,1 - < 0,5 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51, R53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

4. First aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

5. Fire fighting measures

Combustion behaviour:

Non flammable product (flash point is greater than 100°C (CC))

Suitable extinguishing media:

Carbon dioxide, foam, powder

Special protection equipment for firefighters:

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Hazardous combustion products:

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

6. Accidental release measures

Personal precautions:

Avoid skin and eye contact.

Environmental precautions:

Do not let product enter drains.

Clean-up methods:

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.

7. Handling and storage

Handling:

Use only in well-ventilated areas.
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Storage:

Store in original containers at 8-21C (46.4-69.8F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

8. Exposure controls / personal protection**Components with specific control parameters for workplace:**

Valid for

Great Britain

Basis

UK EH40 WELs

Ingredient	ppm	mg/m3	Type	Category	Remarks
CUMENE 98-82-8	25	125	Time Weighted Average (TWA).		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):		EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	ECLTV
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):	Indicative	ECLTV
CUMENE 98-82-8	20	100	Time Weighted Average (TWA).	Indicative	ECLTV

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

The use of chemical resistant gloves such as Nitrile are recommended.

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

General protection and hygiene measures:

Good industrial hygiene practices should be observed.

9. Physical and chemical properties**General characteristics:**

Appearance

Liquid

Blue

Odor:

Characteristic

Phys./chem. properties:

Flash point

> 93 °C (> 199.4 °F)

VOC content

< 3 %

(1999/13/EC)

10. Stability and reactivity**Conditions to avoid:**

Stable

Materials to avoid:

Peroxides.

11. Toxicological information**Oral toxicity:**

May cause irritation to the digestive tract.

Inhalative toxicity:

May cause irritation to respiratory system.

Skin irritation:

Prolonged or repeated contact may cause skin irritation.

Eye irritation:

May cause mild irritation to the eyes.

12. Ecological information**Mobility:**

Cured adhesives are immobile.

Ecotoxicity:

Hazardous components CAS-No.	Species	Exposure time	Value type	Value
Cumene hydroperoxide 80-15-9	Ide, silver or golden orfe (Leuciscus idus) Water flea (Daphnia magna)	48 h	LC 50	14 mg/l
Cumene hydroperoxide 80-15-9		24 h	EC 50	7 mg/l
Cumene 98-82-8	Trout family (Salmonidae)	96 h	LC 50	4,8 mg/l

General ecological information:

Do not empty into drains / surface water / ground water.

Harmful to aquatic organisms.

May cause long-term adverse effects in the aquatic environment.

13. Disposal considerations**Product disposal:**

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Waste code(EWC):

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

14. Transport information**General information:**

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

15. Regulations - classification and identification**Risk phrases:**

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

16. Other information

The labelling of the product is indicated in Section 15. The full text of the R-phrases indicated by codes in this safety data sheet are as follows:

- R10 Flammable.
- R21/22 Harmful in contact with skin and if swallowed.
- R22 Harmful if swallowed.
- R23 Toxic by inhalation.
- R34 Causes burns.
- R37 Irritating to respiratory system.
- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R51 Toxic to aquatic organisms.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R53 May cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R7 May cause fire.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.