

Guided drive DFM-32-100-P-A-GF

Part number: 170860

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	100 mm
Piston diameter	32 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.4 J
Max. force Fy	1227 N
Max. force Fy static	1227 N
Max. force Fz	1227 N
Max. force Fz static	1227 N
Max. moment Mx	47.84 Nm
Max. torque Mx static	47.84 Nm
Max. moment My	35.57 Nm
Max. torque My static	35.57 Nm
Max. moment Mz	35.57 Nm
Max. torque Mz static	35.57 Nm
Max. permissible torque load Mx as a function of stroke	7.08 Nm
Max. effective load dependent upon stroke at defined distance xs	150 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	415 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	482 N

Feature	Value
Moving mass	1564 g
Product weight	3111 g
alternative connections	See product drawing
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel