

Filter regulator MS2-LFR-QS6-D6-C-P-M-AR-MPA-B

Part number: 8086645

FESTO



General operating condition

Data sheet

Feature	Value
Size	2
Series	MS
Actuator lock	Rotary knob with detent
Mounting position	Vertical +/-5°
Grade of filtration	5 µm
Condensate drain	Manual, rotating
Design	Filter regulator with pressure gauge
Max. condensate volume	3 ml
Controller function	Output pressure constant With secondary exhausting With return flow function
Symbol	00991589
Displayable units	MPa
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	With pressure gauge
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Pressure regulation range	0.5 bar ... 7 bar
Max. pressure hysteresis	0.025 MPa
Max. pressure hysteresis	0.25 bar
Max. pressure hysteresis	3.625 psi
Standard nominal flow rate (standardised to DIN 1343)	310 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Storage temperature	-5 °C ... 50 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [6:4:4]
Media temperature	-5 °C ... 50 °C
Ambient temperature	-5 °C ... 50 °C
Product weight	43.5 g
Type of mounting	With accessories
Pneumatic connection, port 1	QS-6
Pneumatic connection, port 2	QS-6
Note on materials	RoHS compliant

Feature	Value
Material seals	NBR
Material rotary knob	POM
Material spring	High-alloy steel
Material filter	Packaging unit
Material housing	Reinforced PA
Material membrane	NBR
Material bowl	Makrolon®
Material separating plate	POM
Material valve stem	Wrought aluminium alloy NBR