

Standards-based cylinder DSBC-...-125- -F1A-

Part number: 8150693

FESTO



 [General operating condition](#)

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	1 mm ... 2800 mm
Piston diameter	125 mm
Piston rod thread	M16
Cushioning	Elastic cushioning rings/plates at both ends Self-adjusting pneumatic end-position cushioning Pneumatic cushioning, adjustable at both ends
Mounting position	optional
Conforms to standard	ISO 15552
Piston-rod end	Male thread Female thread
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Symbol	00991217 00991218 00991235 00991237 00992970 00992971
Variants	Advancing stroke adjustment Weld spatter protection Extended male piston rod thread Piston rod with external hexagon Low friction Sensor slots on 3 profile sides Additional PTFE piston guide
Operating pressure	0.02 MPa ... 1 MPa
Operating pressure	0.2 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	2.6 J ... 3.3 J
Cushioning length	45 mm

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	6881 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	7363 N
Additional weight per piston rod extension of 10 mm	63 g
Additional weight per piston rod thread extension of 10 mm	41 g
Type of mounting	Via female thread With accessories
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material cover	Coated die-cast aluminium
Material piston seal	TPE-U(PU)
Material piston	Wrought aluminium alloy
Material piston rod	High-alloy steel
Material piston rod wiper	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Material of cushioning boss	POM
Material cylinder barrel	Smooth-anodised wrought aluminium alloy
Material nut	Steel, nickel-plated
Material bearing	POM
Material collar screws	Steel, nickel-plated