

# Standards-based cylinder DSBC-125-80-D3-PPSA-N3

Part number: 8165683

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	125 mm
Piston rod thread	M27x2
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	optional
Conforms to standard	ISO 15552
Piston-rod end	Male thread
Design	Piston Piston rod Profile barrel
Position detection	Via proximity switch
Symbol	00992970
Variants	Piston rod at one end
Operating pressure	0.02 MPa ... 1 MPa
Operating pressure	0.2 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	3.3 J
Cushioning length	45 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	6881 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	7363 N
Moving mass	2749 g
Moving mass for 0 mm stroke	2245 g
Additional moving mass per 10 mm stroke	63 g
Product weight	8743 g
Basic weight for 0 mm stroke	6768 g
Additional weight per 10 mm stroke	247 g
Type of mounting	Via female thread With accessories
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Material cover	Coated die-cast aluminium

<b>Feature</b>	<b>Value</b>
Material piston seal	TPE-U(PU)
Material piston	Wrought aluminium alloy
Material piston rod	High-alloy steel
Material piston rod wiper	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Material of cushioning boss	POM
Material cylinder barrel	Smooth-anodised wrought aluminium alloy
Material nut	Galvanised steel
Material rod wiper	TPE-E
Material bearing	Metal polymer compound
Material collar screws	Galvanised steel