

# Compact cylinder ADN-16-10-I-P-A

Part number: 536227

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	16 mm
Piston rod thread	M4
Based on standard	ISO 21287
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston-rod end	Female thread
Position detection	Via proximity switch
Symbol	00991217
Variants	Piston rod at one end
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Operating pressure	14.5 psi ... 145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.15 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	90 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Moving mass	18 g
Product weight	86 g
Type of mounting	With through-hole With female thread With accessories
Pneumatic connection	M5
Note on materials	RoHS compliant
Material collar screws	Steel
Material cover	Anodised wrought aluminium alloy
Material seals	TPE-U(PUR)
Material piston rod	High-alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy