

Compact cylinder ADN-63-15-A-PPS-A

Part number: 572710

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Stroke | 15 mm |
| Piston diameter | 63 mm |
| Piston rod thread | M12x1.25 |
| Cushioning | Self-adjusting pneumatic end-position cushioning |
| Mounting position | Any |
| Conforms to standard | ISO 21287 |
| Piston-rod end | Male thread |
| Position detection | Via proximity switch |
| Symbol | 00992970 |
| Variants | Piston rod at one end |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in end positions | 4.8 J |
| Cushioning length | 7 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 1750 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1870 N |
| Moving mass | 264 g |
| Product weight | 862 g |
| Type of mounting | With through-hole With female thread With accessories |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS compliant |
| Material collar screws | Steel |
| Material cover | Anodised wrought aluminium alloy |
| Material seals | TPE-U(PUR) |
| Material piston rod | High-alloy steel |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |