

# Solenoid valve VMPA2-M1BH-M-PI

Part number: 8022034

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 5/2-way, single solenoid   |
| Type of actuation                                     | Electrical   |
| Valve size  | 20 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 870 l/min  |
| Operating voltage                                     | 24 V DC  |
| Operating pressure                                    | -0.09 MPa ... 1 MPa  |
| Operating pressure                                    | -0.9 bar ... 10 bar  |
| Design  | Piston gate valve  |
| Type of reset   | Pneumatic spring   |
| Approval  | c UL us - Recognised (Oil)   |
| Degree of protection                                  | IP65<br>To IEC 60529   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | Any  |
| Manual override                                       | Detenting<br>Non-detenting   |
| Type of piloting                                      | Piloted  |
| Flow direction  | Reversible   |
| Symbol  | 00991050   |
| lap   | Overlap  |
| Signal status display                                 | Yes  |
| Pilot pressure  | 0.3 MPa ... 0.8 MPa  |
| Pilot pressure  | 3 bar ... 8 bar  |
| Suitability for vacuum                                | Yes  |
| Standard nominal flow rate with QS-10                 | 870 l/min  |
| Switching time off                                    | 28 ms  |
| Switching time on                                     | 15 ms  |
| Max. positive test pulse with 0 signal                | 400 µs   |
| Max. negative test pulse with 1 signal                | 900 µs   |
| Permissible voltage fluctuations                      | +/-25%   |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Vibration resistance                                  | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6           |
| Shock resistance                                      | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                          |
| Corrosion resistance class CRC                        | 1 - Low corrosion stress   |

| <b>Feature</b>                            | <b>Value</b>       |
|---|--------------------|
| LABS (PWIS) conformity                    | VDMA24364-B1/B2-L  |
| Storage temperature                       | -20 °C ... 40 °C   |
| Media temperature                         | -5 °C ... 50 °C    |
| Relative air humidity                     | Max. 90% at 40 °C  |
| Ambient temperature                       | -5 °C ... 50 °C    |
| Max. tightening torque for valve mounting | 0.65 Nm            |
| Product weight                            | 100 g              |
| Type of mounting                          | With through-hole  |
| Note on materials                         | RoHS compliant     |
| Material seals                            | NBR                |
| Material housing                          | Die-cast aluminium |