


Light barrier SOOD-TB-L-PN

Part number: 8075661

FESTO



General operating condition

Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995974
Approval	RCM c UL us - Recognised (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS compliant
Measuring principle	Optoelectronic
Detection method	Through-beam sensor Transmitter Receiver
Type of light	Laser Red
Max. light spot	20 mm with 10000 mm
Operating distance	0 mm ... 10000 mm
Ambient temperature	-20 °C ... 60 °C
Switching output	Push-pull
Switching element function	PNP dark switching NPN light switching
Max. switching frequency	2000 Hz
Max. output current	50 mA
Voltage drop	0 V ... 1.5 V
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 30 V
Residual ripple	10%
No-load supply current	11 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Cable with plug
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	Screw-type lock with AF9
Electrical connection 1, connection pattern	00991155

Feature	Value
Material electrical contact	Gold-plated brass
Cable length	0.15 m
Cable characteristic	Standard
Material cable sheath	TPE-U(PUR)
Type of mounting	With through-hole
Tightening torque	0.5 Nm
Mounting position	Any
Product weight	20 g
Material housing	Makrolon® TPE-U(PU)
Ready status indication	Green LED
Switching status indication	Yellow LED
Function reserve indication	Flashing yellow LED
Degree of protection	IP65 IP67
Insulation voltage	500 V
Immunity to surge	1 kV
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Laser safety class	1
Pollution degree	3