

Retro-reflective sensor SOOE-RG-R-PNLK-T

Part number: 8075667

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995956
Approval	RCM c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS compliant
Measuring principle	Optoelectronic
Detection method	Retro-reflective sensor for transparent objects
Type of light	Red LED
Max. light spot	300 mm with 3500 mm
Operating distance	0 mm ... 3500 mm
Sensor reflector distance	1 ... 5000 mm SARA-R-Q50-S 1 ... 2000 mm SARA-R-Q50-MC 1 ... 1800 mm SARA-RF-Q100-S 1 ... 3300 mm SARA-RF-Q100-MC 1 ... 2000 mm SARA-R-Q20-S 1 ... 1800 mm SARA-R-Q20-MC 1 ... 1100 mm SARA-R-Q14-M 1 ... 1400 mm SARA-R-D20-M
Ambient temperature	-20 °C ... 60 °C
Reference material	Reference reflector: SARA-R-Q50-S
Switching output	Push-pull
Switching element function	Switchable PNP dark switching NPN light switching
Max. switching frequency	500 Hz
Max. output current	100 mA
Voltage drop	0 V ... 1.5 V
Timer function	Via IO-Link®
Short circuit current rating	Pulsed
Protocol	IO-Link®
IO-Link, Protocol version	Device V 1.1
IO-Link, communication mode	COM2 (38.4 kBaud)
IO-Link, SIO-Mode support	Yes

Feature	Value
IO-Link, Port class	A
IO-Link, Process data length OUT	2 bit
IO-Link, Process data content OUT	1 bit (emitter disable) 1 bit (Hold)
IO-Link, Process data length IN	2 bit
IO-Link, Process data content IN	1 bit (Stability Alarm) 1 bit SSC (Switching Signal)
IO-Link, Min. cycle time	2.3 ms
IO-Link, Data storage required	2000 Byte
Operational voltage range DC	10 V ... 30 V
Residual ripple	10%
No-load supply current	25 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00991155
Material electrical contact	Gold-plated brass
Type of mounting	Via through-hole for M3 screw
Tightening torque	0.8 Nm
Mounting position	Any
Product weight	10 g
Material housing	Makrolon® PLEXIGLAS®
Ready status indication	Green LED
Switching status indication	Yellow LED
Function reserve indication	Flashing yellow LED
Setting options	IO-Link® Poti Teach-in
Degree of protection	IP65 IP67 IP69K
Insulation voltage	500 V
Immunity to surge	1 kV
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pollution degree	3