

Angle seat valve VZXF-L-M22C-M-B-G2-450-M1-V4V4T-50-3

FESTO

Part number: 1002523



General operating condition

Data sheet

| Feature | Value |
|----------------------------------|--|
| Structural design | Poppet valve with piston actuator |
| Actuation type | Pneumatic |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | In-line installation |
| Cable connection | Threaded sleeve G2 as per DIN ISO 228 |
| Nominal width | 45 mm |
| Valve function | 2/2-way, closed, monostable |
| Flow direction | Non-reversible |
| Medium pressure | 0 MPa ... 0.3 MPa |
| Medium pressure | 0 bar ... 3 bar |
| Nominal pressure of fitting PN | 40 |
| Exhaust air function | Cannot be throttled |
| Reset method | Mechanical spring |
| Type of control | Externally controlled |
| Pneumatic connection | Internal thread G1/8 |
| Operating pressure | 0.6 MPa ... 1 MPa |
| Operating pressure | 6 bar ... 10 bar |
| Operating pressure | 87 psi ... 145 psi |
| Symbol | 00991367 |
| Medium | Vapor Hydraulic fluid based on mineral oil Inert gas Mineral oil Water Filtered compressed air, 200 µm filter mesh Neutral liquids |
| Flow direction | Under valve seat, for gaseous and liquid media |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Max. viscosity | 600 mm ² /s |
| Temperature of medium | -40 °C ... 200 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Flow rate Kv | 19.5 m ³ /h |
| Note on materials | RoHS compliant |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Valve housing material | Cast stainless steel |
| Material number, fitting housing | 1,4408 |

| Feature | Value |
|--|--|
| Spindle seal material | PTFE |
| Seat seal material | PTFE |
| Product weight | 3500 g |
| CE marking (see declaration of conformity) | as per EU pressure equipment directive |
| UKCA marking (see declaration of conformity) | according to UK regulations for pressure equipment |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| Drive housing material | high-alloy stainless steel |