


Pneumatic valve

JDH-5-1/4

Part number: 10409

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/2-way, dominant, bistable |
| Actuation type | Pneumatic |
| Width | 30.5 mm |
| Normal nominal flow rate (normalized to DIN 1343) | 1100 l/min |
| Pneumatic working port | G1/4 |
| Operating pressure | 0 MPa ... 0.8 MPa |
| Operating pressure | 0 bar ... 8 bar |
| Structural design | Plate seat |
| Degree of protection | IP65 |
| Nominal width | 7 mm |
| Width dimension | 32 mm |
| Exhaust air function | Adjustable |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of control | directly |
| Pilot air supply port | External |
| Flow direction | Non-reversible |
| Symbol | 00995764 |
| Lap | Negative overlap |
| Pilot pressure MPa | 0.23 MPa ... 1 MPa |
| Pilot pressure | 2.3 bar ... 10 bar |
| Max. switching frequency | 12 Hz |
| Changeover time | 12 ms |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 60 °C |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 330 g |
| Type of mounting | On terminal strip With through-hole |
| Pilot air port 12 | G1/8 |
| Pilot air port 14 | G1/8 |
| Pneumatic connection 1 | G1/4 |

| Feature | Value |
|------------------------|-------------------|
| Pneumatic connection 2 | G1/4 |
| Pneumatic connection 3 | G1/4 |
| Pneumatic connection 4 | G1/4 |
| Pneumatic connection 5 | G1/4 |
| Note on materials | RoHS compliant |
| Seals material | NBR TPE-U(PU) |
| Housing material | Die-cast aluminum |