

Air solenoid valve MFH-3-1/4-NPT

Part number: 10836

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Valve function	3/2-way, closed, monostable
Actuation type	Electrical
Width	30.5 mm
Normal nominal flow rate (normalized to DIN 1343)	800 l/min
Pneumatic working port	1/4 NPT
Operating voltage	Via solenoid coil, to be ordered separately
Operating pressure	0.15 MPa ... 0.8 MPa
Operating pressure	1.5 bar ... 8 bar
Structural design	Plate seat
Reset method	Mechanical spring
Certification	c UL us - recognized (OL)
Degree of protection	IP65
Nominal width	7 mm
Width dimension	32 mm
Exhaust air function	Adjustable
Sealing principle	Soft
Mounting position	Any
Manual override	Detenting
Type of control	Piloted
Flow direction	Non-reversible
Symbol	00991041
Lap	Negative overlap
Switching time off	29 ms
On switching time	10 ms
Max. positive test pulse with 0 signal	2200 µs
Max. negative test pulse on 1 signal	3700 µs
Coil characteristics	See solenoid coil, to be ordered separately
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-5 °C ... 40 °C
Product weight	320 g
Electrical connection	Via F coil, to be ordered separately

Feature	Value
Type of mounting	On terminal strip With through-hole
Pilot exhaust air port 82	M5
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Pneumatic connection 3	1/4 NPT
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Die-cast aluminum