

ISO cylinder CRDSNU-B-16-10-P-A-MG-A1

Part number: 8073759

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 10 mm |
| Piston diameter | 16 mm |
| Based on standard | ISO 6432 |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | Any |
| Design | Piston Piston rod Cylinder barrel |
| Position detection | Via proximity switch |
| Symbol | 00991217 |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 4 - Very high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | 0 °C ... 80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 104 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 121 N |
| Moving mass for 0 mm stroke | 21 g |
| Additional moving mass per 10 mm stroke | 2.2 g |
| Basic weight for 0 mm stroke | 130 g |
| Additional weight per 10 mm stroke | 4.8 g |
| Type of mounting | With accessories |
| Pneumatic connection | M5 |
| Note on materials | RoHS compliant |
| Material cover | High-alloy stainless steel |
| Material piston rod | High-alloy stainless steel |
| Material cylinder barrel | High-alloy stainless steel |