

Pneumatic valve

J-5/2-3/4-D-4

Part number: 12462

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Valve function	5/2-way, bistable
Actuation type	Pneumatic
Width	76 mm
Normal nominal flow rate (normalized to DIN 1343)	6000 l/min
Pneumatic working port	Sub-base, size 4 as per ISO 5599-1 G3/4
Operating pressure	-0.9 bar ... 16 bar
Structural design	Piston gate valve
Nominal width	18 mm
Width dimension	82 mm
Exhaust air function	Adjustable
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 5599-1
Manual override	None
ISO code	401
Type of control	directly
Flow direction	Reversible
Symbol	00991037
Lap	Positive overlap
Pilot pressure	2 bar ... 16 bar
Changeover time	20 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 60 °C
Noise level	85 dB(A)
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 60 °C
Product weight	1800 g
Type of mounting	On sub-base With through-hole and screw
Pilot air port 12	Sub-base, size 4 as per ISO 5599-1
Pilot air port 14	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 1	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 2	Sub-base, size 4 as per ISO 5599-1

Feature	Value
Pneumatic connection 3	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 4	Sub-base, size 4 as per ISO 5599-1
Pneumatic connection 5	Sub-base, size 4 as per ISO 5599-1
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Aluminum