


Light barrier SOOE-TB-L-PNLK-T

Part number: 8075671

FESTO



General operating condition

Data sheet

Feature	Value
Design	Block design
Conforms to standard	EN 60947-5-2
Symbol	00995973
Approval	RCM c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Certificate issuing authority	UL E232949
Note on materials	RoHS compliant
Measuring principle	Optoelectronic
Detection method	Through-beam sensor Transmitter Receiver
Type of light	Laser Red
Max. light spot	50 mm with 20000 mm
Operating distance	0 mm ... 20000 mm
Ambient temperature	-40 °C ... 60 °C
Switching output	Push-pull
Switching element function	Switchable PNP dark switching NPN light switching
Max. switching frequency	1250 Hz
Max. output current	100 mA
Voltage drop	0 V ... 1.5 V
Timer function	Via IO-Link®
Short circuit current rating	Pulsed
Protocol	IO-Link®
IO-Link, Protocol version	Device V 1.1
IO-Link, communication mode	COM2 (38.4 kBaud)
IO-Link, SIO-Mode support	Yes
IO-Link, Port class	A
IO-Link, Process data length OUT	1 bit (Emitter) 2 bit (Receiver)

Feature	Value
IO-Link, Process data content OUT	1 bit (emitter disable) 1 bit (Hold)
IO-Link, Process data length IN	2 bit (Receiver)
IO-Link, Process data content IN	1 bit (Stability Alarm) 1 bit SSC (Switching Signal)
IO-Link, Min. cycle time	2.3 ms
IO-Link, Data storage required	2000 Byte
Operational voltage range DC	10 V ... 30 V
Residual ripple	10%
No-load supply current	14 mA
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Plug
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	3
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00991155
Material electrical contact	Gold-plated brass
Type of mounting	Via through-hole for M3 screw
Tightening torque	0.8 Nm
Mounting position	Any
Product weight	20 g
Material housing	Makrolon® PLEXIGLAS®
Ready status indication	Green LED
Switching status indication	Yellow LED
Function reserve indication	Flashing yellow LED
Setting options	IO-Link® Poti Teach-in
Degree of protection	IP65 IP67 IP69K
Insulation voltage	500 V
Immunity to surge	1 kV
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Laser safety class	1
Pollution degree	3