

# Angled gripper DHWS-40-A-NC

Part number: 1310185

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	40
Max. interchangeability	≤0.2 mm
Max. opening angle	40 deg
Rotational symmetry	≤0.2 mm
Pneumatic gripper repetition accuracy	≤0.04 mm
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Bracket
Gripping force backup	During closing
Structural design	Lever
Position sensing	Via proximity switch
Symbol	00991895
Operating pressure	4 bar ... 8 bar
Max. operating frequency of pneumatic gripper	≤3 Hz
Min. opening time at 6 bar	99 ms
Min. closing time at 6 bar	69 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. This excludes printed circuit boards, cables, electrical connectors and coils.
Ambient temperature	5 °C ... 60 °C
Mass moment of inertia	3.87 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	200 N
Maximum torque on gripper jaw, Mx static	13 Nm
Maximum torque on gripper jaw, My static	13 Nm
Maximum torque on gripper jaw, Mz static	13 Nm
Product weight	790 g
Type of mounting	Alternatively: With internal thread and centering sleeve Via through-hole and centering sleeve
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Cover cap material	PA

<b>Feature</b>	<b>Value</b>
Housing material	Wrought aluminum alloy Hard-anodized
Gripper jaw material	High-alloy steel