


Rotary/lifting module EHMB-32-200

Part number: 1098559

FESTO



 General operating condition

Data sheet

Feature	Value
Drive pinion diameter	12 mm
Working stroke	0 mm ... 200 mm
Size	32
Rotation angle	Infinite
Toothed belt pitch	5 mm
Mounting position	Any
Gearbox type	Belt drive
Structural design	With toothed belt
Gear ratio	3:1
Position sensing	For inductive sensors
Max. output speed	300 rpm
Max. input speed	900 rpm
Max. speed	1.5 m/s
Repetition accuracy	±0.03°
Noise level	51 dB(A)
Information on the sound pressure level	with covering: 53 [dB (A)]
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	10000 kgcm ²
Max. output torque	20 Nm
Max. driving torque	6.7 Nm
Max. feed force F _x	750 N
No-load driving torque	<0.5 Nm
Guide value for payload, horizontal	8 kg
Guide value for payload, vertical	15 kg
Product weight	6388 g
Moving mass	2058 g
Material of drive shaft	Steel
Note on materials	RoHS compliant
Material of flange	Wrought aluminum alloy, anodized
Drive shaft material	high-alloy stainless steel
Cover material	Wrought aluminum alloy Anodized
Housing material	Anodized
Retaining material	Wrought aluminum alloy, anodized
Retainer bracket material	Wrought aluminum alloy, anodized

Feature	Value
Toothed belt material	Neoprene with glass fiber