


# Rotary/lifting module EHMB-20-100

Part number: 1107096

FESTO



## Data sheet

 General operating condition

Feature	Value
Drive pinion diameter	6 mm
Working stroke	0 mm ... 100 mm
Size	20
Rotation angle	Infinite
Toothed belt pitch	2 mm
Mounting position	Any
Gearbox type	Belt drive
Structural design	With toothed belt
Gear ratio	4.5:1
Position sensing	For inductive sensors
Max. output speed	300 rpm
Max. input speed	1350 rpm
Max. speed	1.5 m/s
Repetition accuracy	±0.03°
Noise level	54 dB(A)
Information on the sound pressure level	with covering: 57 [dB (A)]
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	1000 kgcm <sup>2</sup>
Max. output torque	3.15 Nm
Max. driving torque	0.7 Nm
Max. feed force F <sub>x</sub>	480 N
No-load driving torque	<0.07 Nm
Guide value for payload, horizontal	3 kg
Guide value for payload, vertical	3 kg
Product weight	1716 g
Moving mass	705 g
Material of drive shaft	Steel
Note on materials	RoHS compliant
Material of flange	Wrought aluminum alloy, anodized
Drive shaft material	high-alloy stainless steel
Cover material	Wrought aluminum alloy Anodized
Housing material	Anodized
Retaining material	Wrought aluminum alloy, anodized
Retainer bracket material	Wrought aluminum alloy, anodized

Feature	Value
Toothed belt material	Neoprene with glass fiber