

Bellows gripper DHEB-18-E-D-S-P

Part number: 1320780

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | 18 |
| Stroke of bellows | 7.5 mm |
| Min. diameter to be gripped | 19.5 mm |
| Max. diameter to be gripped | 25 mm |
| Mounting position | Any |
| Mode of operation | Single-acting Closed |
| Gripper function | Adaptive |
| Structural design | Contracting diaphragm Positively driven motion sequence |
| Guide | Basic guide |
| Position sensing | None |
| Operating pressure | 5 bar ... 8 bar |
| Resetting pressure | <1 bar |
| Max. operating frequency of pneumatic gripper | ≤4 Hz |
| Min. opening time at 6 bar | 20 ms |
| Min. closing time at 6 bar | 50 ms |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| For use in the food industry | See supplementary material information |
| Ambient temperature | 5 °C ... 60 °C |
| Average replacement interval for the bellows | 1 MioCyc |
| Guide value for payload | 0.21 kg |
| Product weight | 28 g |
| Type of mounting | With external thread With lock nut |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Bellows material | VMQ (silicone) |
| Housing material | Aluminum Anodized |