

Push-in L-fitting, long QSMLL-M3-2

Part number: 133032

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Mini |
| Nominal width | 0.8 mm |
| Tubing insertion depth | 8.4 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | Any |
| Design | L-shape, long |
| Pack size | 10 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa ... 0.6 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 6 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 87 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 80 °C |
| Nominal tightening torque | 0.48 Nm |
| Tolerance for nominal tightening torque | ± 55% |
| Product weight | 2.7 g |
| Type of mounting | External hexagon, AF 5.5 |
| Pneumatic connection 1 | External thread M3 |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 2 mm |
| Releasing ring color | Blue |
| Material of screwed plug | Brass, nickel-plated |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |