

Flat cylinder DZH-32-80-PPV-A

Part number: 14044

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	32 mm Equivalent diameter
Piston rod thread	M10x1.25
Max. angle of rotation of the piston rod +/-	1.7 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991235
Variants	Piston rod at one end
Protection against torsion/guide	Oval piston
Operating pressure	0.06 MPa ... 1 MPa
Operating pressure	0.6 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 80 °C
Cushioning length	19 mm
Max. torque for protection against rotation	1 Nm
Theoretical force at 6 bar, retracting	415 N
Theoretical force at 6 bar, advancing	483 N
Moving mass	196 g
Product weight	711 g
Additional weight per 10 mm stroke	25 g
Basic weight with 0 mm stroke	511 g
Type of mounting	With internal thread With accessories
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Cover material	Aluminum
Seals material	TPE-U(PU)
Housing material	Aluminum

Feature	Value
Piston seal material	TPE-U(PU)
Piston rod material	High-alloy steel