

# Flat cylinder DZH-40-25-PPV-A

Part number: 14052

FESTO



[PDF General operating condition](#)

## Data sheet

| Feature                                      | Value                                                              |
|----------------------------------------------|--------------------------------------------------------------------|
| Stroke                                       | 25 mm                                                              |
| Piston diameter                              | 40 mm<br>Equivalent diameter                                       |
| Piston rod thread                            | M12x1.25                                                           |
| Max. angle of rotation of the piston rod +/- | 1.4 deg                                                            |
| Cushioning                                   | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                            | Any                                                                |
| Mode of operation                            | Double-acting                                                      |
| Structural design                            | Piston<br>Piston rod                                               |
| Position sensing                             | Via proximity switch                                               |
| Symbol                                       | 00991235                                                           |
| Variants                                     | Piston rod at one end                                              |
| Protection against torsion/guide             | Oval piston                                                        |
| Operating pressure                           | 0.06 MPa ... 1 MPa                                                 |
| Operating pressure                           | 0.6 bar ... 10 bar                                                 |
| Operating medium                             | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media     | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)             | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                       | VDMA24364-B2-L                                                     |
| Ambient temperature                          | -20 °C ... 80 °C                                                   |
| Cushioning length                            | 21 mm                                                              |
| Max. torque for protection against rotation  | 1.2 Nm                                                             |
| Theoretical force at 6 bar, retracting       | 633 N                                                              |
| Theoretical force at 6 bar, advancing        | 754 N                                                              |
| Moving mass                                  | 276 g                                                              |
| Product weight                               | 928 g                                                              |
| Additional weight per 10 mm stroke           | 37 g                                                               |
| Basic weight with 0 mm stroke                | 836 g                                                              |
| Type of mounting                             | With internal thread<br>With accessories                           |
| Pneumatic connection                         | G1/4                                                               |
| Note on materials                            | RoHS compliant                                                     |
| Cover material                               | Aluminum                                                           |
| Seals material                               | TPE-U(PU)                                                          |
| Housing material                             | Aluminum                                                           |

| <b>Feature</b>       | <b>Value</b>     |
|----------------------|------------------|
| Piston seal material | TPE-U(PU)        |
| Piston rod material  | High-alloy steel |