

Rotary actuator DSM-16-270-CC-HD-A-B

Part number: 1369123

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Size | 16 |
| Cushioning angle | 12 deg |
| Adjustment range of swivel angle | 0 deg ... 246 deg |
| Swivel angle | 0 deg ... 246 deg |
| Permissible stop radius | ≥17 mm |
| Cushioning | Pneumatic shock absorber at both ends |
| Mounting position | Any |
| Precision adjustment | -3 deg |
| Mode of operation | Double-acting |
| Structural design | Rotary vane |
| Position sensing | Via proximity switch |
| Symbol | 00991265 |
| Operating pressure | 0.3 MPa ... 1 MPa |
| Operating pressure | 3 bar ... 10 bar |
| Max. swivel frequency at 6 bar | 1 Hz |
| Repetition accuracy | 0.1 deg |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. stop force | 160 N |
| Max. axial force | 290 N |
| Max. radial force | 300 N |
| Theoretical torque at 6 bar | 2.5 Nm |
| Permissible mass moment of inertia | 0.02 kgm ² |
| Product weight | 705 g |
| Type of mounting | With internal thread |
| Pneumatic connection | M5 |
| Note on materials | RoHS compliant |
| Drive shaft material | Steel Nickel-plated |
| Seals material | TPE-U(PU) |
| Housing material | Anodized aluminum |