

Flat cylinder DZH-63-160-PPV-A

Part number: 14080

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Stroke	160 mm
Piston diameter	63 mm Equivalent diameter
Piston rod thread	M16x1.5
Max. angle of rotation of the piston rod +/-	0.67 deg
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Symbol	00991235
Variants	Piston rod at one end
Protection against torsion/guide	Oval piston
Operating pressure	0.06 MPa ... 1 MPa
Operating pressure	0.6 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 80 °C
Cushioning length	23 mm
Max. torque for protection against rotation	2 Nm
Theoretical force at 6 bar, retracting	1682 N
Theoretical force at 6 bar, advancing	1870 N
Moving mass	951 g
Product weight	2934 g
Additional weight per 10 mm stroke	69.6 g
Basic weight with 0 mm stroke	1820 g
Type of mounting	With internal thread With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Aluminum
Seals material	TPE-U(PU)
Housing material	Aluminum

Feature	Value
Piston seal material	TPE-U(PU)
Piston rod material	High-alloy steel