

# Air solenoid valve

## VZWD-L-M22C-M-N18-15-V-1P4-85-R1

FESTO

Part number: 1491888



[PDF](#) General operating condition

## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Structural design                | Directly actuated poppet valve   |
| Actuation type                   | Electrical   |
| Sealing principle                | Soft   |
| Mounting position                | Any  |
| Type of mounting                 | In-line installation   |
| Fitting connection               | 1/8 NPT  |
| Electrical connection            | Plug<br>As per EN 175301-803<br>Rectangular design   |
| Nominal width                    | 1.5 mm   |
| Valve function                   | 2/2-way, closed, monostable  |
| Manual override                  | None   |
| Flow direction                   | Non-reversible   |
| Medium                           | Compressed air as per ISO 8573-1:2010 [7:4:4]<br>Inert gas<br>Mineral oil<br>Water<br>Neutral liquids<br>Other flow media on request |
| Nominal pressure of fitting PN   | 100  |
| Pressure difference              | 0 MPa  |
| Differential pressure            | 0 bar  |
| Pressure difference              | 0 psi  |
| Coil characteristics             | 24 V DC: 11.0 W  |
| Insulation class                 | H  |
| Permissible voltage fluctuations | +/- 10%  |
| Duty cycle                       | 100%   |
| Reset method                     | Mechanical spring  |
| Type of control                  | directly   |
| Symbol                           | 00992979   |
| Medium pressure                  | 0 MPa ... 8.5 MPa  |

| Feature   | Value                      |
|---|----------------------------|
| Medium pressure                                   | 0 bar ... 85 bar           |
| Medium pressure                                   | 0 psi ... 1232.5 psi       |
| Max. viscosity                                    | 22 mm <sup>2</sup> /s      |
| Temperature of medium                             | -10 °C ... 80 °C           |
| Ambient temperature                               | -10 °C ... 35 °C           |
| Leak rate to EN 12266-1                           | A                          |
| Flow rate Kv                                      | 0.09 m <sup>3</sup> /h     |
| Normal nominal flow rate (normalized to DIN 1343) | 95 l/min                   |
| On switching time                                 | 20 ms                      |
| Switching time off                                | 18 ms                      |
| Note on materials                                 | RoHS compliant             |
| LABS (PWIS) conformity                            | VDMA24364 Zone III         |
| Housing material                                  | high-alloy stainless steel |
| Material number of housing                        | 1,4305                     |
| Seals material                                    | FPM                        |
| Armature tube material                            | High-alloy steel           |
| Product weight                                    | 500 g                      |
| Degree of protection                              | IP65                       |
| Corrosion resistance class (CRC)                  | 3 - High corrosion stress  |
| Max. tightening torque for connecting thread      | 10 Nm                      |
| Max. tightening torque for coil fastening         | 2 Nm                       |