

# Air solenoid valve

## VZWP-L-M22C-G34-250-3AP4-40

FESTO

Part number: 1489963



 General operating condition

## Data sheet

Feature	Value
Structural design	Pilot-controlled piston poppet valve
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Coil preferably on top
Type of mounting	In-line installation
Fitting connection	G3/4
Electrical connection	Plug As per EN 175301-803 Rectangular design
Nominal width	25 mm
Valve function	2/2-way, closed, monostable
Manual override	None
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Neutral liquids Other flow media on request
Nominal pressure of fitting PN	40
Pressure difference	0.05 MPa
Differential pressure	0.5 bar
Pressure difference	7.25 psi
Coil characteristics	230 V AC: 50/60 Hz, initial power 10.5 VA, holding power 7.6 VA
Insulation class	H
Permissible voltage fluctuations	+/- 10%
Duty cycle	100%
Type of control	Piloted
Symbol	00992974
Medium pressure	0.05 MPa ... 4 MPa
Medium pressure	0.5 bar ... 40 bar
Medium pressure	7.25 psi ... 580 psi
Max. viscosity	22 mm <sup>2</sup> /s

Feature	Value
Temperature of medium	-10 °C ... 80 °C
Ambient temperature	-10 °C ... 35 °C
Leak rate to EN 12266-1	A
Flow rate Kv	8.2 m <sup>3</sup> /h
Normal nominal flow rate (normalized to DIN 1343)	8750 l/min
On switching time	130 ms
Switching time off	300 ms
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 Zone III
Housing material	Cast brass
Material number of housing	CW617N
Seals material	NBR
Material of screws	high-alloy stainless steel
Material number of screw	1,4301
Product weight	1500 g
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Degree of protection	IP65
Corrosion resistance class (CRC)	1 - Low corrosion stress