


# Vacuum switch VPEV-1/8

Part number: 150261

FESTO



[PDF General operating condition](#)

## Data sheet

Feature	Value
Conforms to standard	EN 60947-5-1
Symbol	00991471
Certification	CCC
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Note on materials	RoHS compliant
Measured variable	Relative pressure
Method of measurement	Pneumatic/electric pressure transducer
Pressure measuring range	-0.1 MPa ... 0.16 MPa
Pressure measuring range	-1 bar ... 1.6 bar
Pressure measuring range	-14.5 psi ... 23.2 psi
Operating pressure	-0.1 MPa ... 0.16 MPa
Operating pressure	-1 bar ... 1.6 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-20 °C ... 80 °C
Ambient temperature	-20 °C ... 80 °C
Switching element function	Changeover switch
Max. switching frequency	3 Hz
Max. switching output voltage AC	250 V
Max. switching output voltage DC	125 V
Max. output current	5000 mA
Minimum load current	1 mA at 24 V 10 mA at 10 V 100 mA at 5V
Utilization category for inductive load	AC-14 DC-13
Utilization category for ohmic load	AC-12 DC-12

Feature	Value
Electrical connection	Type A Plug As per DIN 43650 Rectangular design
Type of mounting	With through-hole
Mounting position	Any
Pneumatic connection	G1/8
Product weight	240 g
Housing material	Wrought aluminum alloy
Switching contact material	Silver
Switching status indication	Yellow LED
Setting range threshold value	-0.95 bar ... -0.2 bar
Setting range threshold value after conversion	0.16 bar ... 1.6 bar
Degree of protection	IP65
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L