

Proximity sensor SIES-V3B-PS-S-L

Part number: 150491

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991701 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| Rated operating distance | 2 mm |
| Assured operating distance | 1.6 mm |
| Reduction factors | Aluminum = 0.45 Stainless steel St 18/8 = 0.7 Copper = 0.3 Brass = 0.5 Steel St 37 = 1.0 |
| Ambient temperature | -25 °C ... 85 °C |
| Repetition accuracy | 0.1 mm |
| Switching output | PNP |
| Switching element function | N/O contact |
| Max. switching frequency | 1200 Hz |
| Max. switching frequency DC | 1200 Hz |
| Max. output current as a function of temperature | 200 mA at ≤ 50 °C 150 mA at ≤ 85 °C |
| Voltage drop | 3.2 V |
| Short-circuit protection | Pulsed |
| DC operating voltage range | 10 V ... 30 V |
| Residual ripple | 10 % |
| Idle current | ≤30 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, connection technology | M8x1 A-coded as per EN 61076-2-104 |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, type of mounting | not rotatable |
| Electrical connection 1, type of mounting | Compatible with snap-locking Compatible with rotatable screw-type lock |
| Size | 15x20x30 mm |
| Type of mounting | With through-hole |
| Mounting type | Flush |
| Product weight | 120 g |

| Feature | Value |
|--|----------------|
| Housing material | Die-cast zinc |
| Switching status indication | LED yellow |
| Degree of protection | IP67 |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Selection of additional sensor information | Special design |
| Electrical output | PNP |
| Selection of sensor version | Standard |