

Proximity sensor SIEN-6,5B-PO-S-L

Part number: 150383

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991614 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | according to UK RoHS regulations (UK-R) |
| Rated operating distance | 1.5 mm |
| Assured operating distance | 1.21 mm |
| Reduction factors | Aluminum = 0.25 Stainless steel St 18/8 = 0.7 Copper = 0.2 Brass = 0.35 Steel St 37 = 1.0 |
| Ambient temperature | -25 °C ... 70 °C |
| Repetition accuracy under constant conditions | 0.07 mm |
| Switching output | PNP |
| Switching element function | N/C contact |
| Hysteresis | ≤0.07 mm |
| Max. switching frequency | 5000 Hz |
| Max. output current | 200 mA |
| Voltage drop | ≤2 V |
| Inductive protective circuit | Installed |
| Short-circuit protection | Pulsed |
| DC operating voltage range | 10 V ... 30 V |
| Residual ripple | ± 10% |
| Idle current | ≤10 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, connection technology | M8x1 A-coded as per EN 61076-2-104 |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, type of mounting | not rotatable |
| Electrical connection 1, type of mounting | Compatible with snap-locking Compatible with rotatable screw-type lock |
| Size | 6.5 mm |
| Type of mounting | Clamped |
| Mounting type | Flush |
| Product weight | 4 g |

| Feature | Value |
|--|---|
| Housing material | High-alloy stainless steel Chrome-plated |
| Switching status indication | LED yellow |
| Ambient temperature with flexible cable installation | -5 °C ... 70 °C |
| Degree of protection | IP65 IP67 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Selection of additional sensor information | With standard switching distance |
| Electrical output | PNP |
| Selection of sensor version | Standard |