


Proximity sensor SIEN-M18B-NO-K-L

Part number: 150420

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|---|
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991643 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| CE marking (see declaration of conformity) | As per EU EMC directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | according to UK RoHS regulations (UK-R) |
| Note on materials | RoHS-compliant |
| Rated operating distance | 5 mm |
| Assured operating distance | 4.05 mm |
| Reduction factors | Aluminum = 0.4 Stainless steel St 18/8 = 0.8 Copper = 0.4 Brass = 0.5 Steel St 37 = 1.0 |
| Ambient temperature | -25 °C ... 70 °C |
| Repetition accuracy | 0.25 mm |
| Switching output | NPN |
| Switching element function | N/C contact |
| Hysteresis | ≤0.55 mm |
| Max. switching frequency | 2000 Hz |
| Max. output current | 200 mA |
| Voltage drop | 2 V |
| Short-circuit protection | Pulsed |
| DC operating voltage range | 10 V ... 30 V |
| Residual ripple | +/- 20 % |
| Idle current | ≤10 mA |
| Reverse polarity protection | for all electrical connections |
| Electrical connection 1, connection type | Cable |
| Electrical connection 1, connection technology | Open end |
| Electrical connection 1, number of pins/wires | 3 |
| Cable length | 2.5 m |
| Material of cable sheath | TPE-U(PUR) |
| Size | M18x1 |
| Type of mounting | With lock nut |
| Tightening torque | 20 Nm |
| Mounting type | Flush |

| Feature | Value |
|--|----------------------------------|
| Product weight | 108 g |
| Housing material | PBTP Nickel-plated |
| Switching status indication | LED yellow |
| Ambient temperature with flexible cable installation | -5 °C ... 70 °C |
| Degree of protection | IP67 |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Contamination level | 3 |
| Selection of additional sensor information | With standard switching distance |
| Electrical output | NPN |
| Selection of sensor version | Standard |