



Proximity sensor SME-1-S-24-B

Part number: 150850

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Design	Block design
Symbol	00995365
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Magnetic reed
Ambient temperature	-20 °C ... 70 °C
Repetition accuracy	0.2 mm
Switching output	Contact-based, bipolar
Switching element function	N/O contact
On time	≤0.5 ms
Max. switching frequency	500 Hz
Max. output current	1000 mA
Min. switching capacity AC	27 VA
Max. switching capacity DC	27 W
Short-circuit protection	no
Overload protection	Not available
DC operating voltage range	0 V ... 30 V
Reverse polarity protection	no
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M8x1 A-coded as per EN 61076-2-104
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	not rotatable
Electrical connection 1, type of mounting	Compatible with snap-locking Compatible with rotatable screw-type lock
Electrical connection for input 1, connection pattern	00992826
Connection outlet orientation	Longitudinal
Type of mounting	With accessories
Mounting position	Any
Product weight	45 g
Housing colour	Black
Housing material	PET Steel Steel, galvanized Die-cast zinc

Feature	Value
Ambient temperature with flexible cable installation	-5 °C ... 70 °C
Degree of protection	IP67
LABS (PWIS) conformity	VDMA24364-B2-L