

Compact cylinder AEVUZ-63- -A-P-A

Part number: 156487

FESTO



 General operating condition

Data sheet

Overall data sheet – Individual values depend upon your configuration.

| Feature | Value |
|--|--|
| Stroke | 1 mm ... 25 mm |
| Piston diameter | 63 mm |
| Piston rod thread | M12x1.25 |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Single-acting Pulling |
| Piston rod end | External thread |
| Structural design | Piston Piston rod |
| Position sensing | For proximity sensor |
| Symbol | 00991204 |
| Variants | Piston rod at one end |
| Operating pressure | 0.08 MPa ... 1 MPa |
| Operating pressure | 0.8 bar ... 10 bar |
| Operating pressure | 11.6 psi ... 145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.7 J |
| Theoretical force at 6 bar, advancing | 1679 N |
| Moving mass at 0 mm stroke | 134 g |
| Additional moving mass per 10 mm stroke | 16 g |
| Basic weight with 0 mm stroke | 1059 g |
| Additional weight per 10 mm stroke | 107 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection | G1/8 |
| Flange screws material | Steel, galvanized |
| Cover material | Wrought aluminum alloy |
| Material of dynamic seals | NBR TPE-U(PU) |
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | Wrought aluminum alloy |