

Compact cylinder ADVUL-25-40-P-A

Part number: 156872

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Stroke | 40 mm |
| Piston diameter | 25 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Structural design | Piston Piston rod |
| Position sensing | Via proximity switch |
| Symbol | 00991737 |
| Variants | Piston rod at one end |
| Protection against torsion/guide | Guide rod with yoke |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.1 J |
| Theoretical force at 6 bar, retracting | 247 N |
| Theoretical force at 6 bar, advancing | 295 N |
| Moving mass at 0 mm stroke | 61 g |
| Additional moving mass per 10 mm stroke | 11 g |
| Basic weight with 0 mm stroke | 215 g |
| Additional weight per 10 mm stroke | 28 g |
| Type of mounting | With through-hole With accessories |
| Pneumatic connection | M5 |
| Flange screws material | Steel, galvanized |
| Cover material | Wrought aluminum alloy |
| Material of dynamic seals | NBR TPE-U(PU) |
| Piston rod material | high-alloy stainless steel |
| Material of cylinder barrel | Wrought aluminum alloy |