

Service unit FRC-1/8-D-MINI

Part number: 159604

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Mini |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Vertical $\pm 5^\circ$ |
| Condensate drain | Manual, rotating |
| Structural design | Proportional standard oil mist lubricator |
| Max. condensate volume | 22 ml |
| Grade of filtration | 40 μm |
| Bowl guard | Metal bowl guard |
| Symbol | 00991549 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 0.1 MPa ... 1.6 MPa |
| Operating pressure | 1 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.02 MPa |
| Max. pressure hysteresis | 0.2 bar |
| Max. pressure hysteresis | 2.9 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 700 l/min |
| Operating medium | Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:-] Inert gases |
| Temperature of medium | -10 $^\circ\text{C}$... 60 $^\circ\text{C}$ |
| Ambient temperature | -10 $^\circ\text{C}$... 60 $^\circ\text{C}$ |
| Product weight | 660 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | G1/8 |
| Note on materials | RoHS compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |