

Trunnion support CRLNZG-40/50

Part number: 161875

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	40/50
Based on norm	ISO 15552
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	2.5 kN
Product weight	323 g
Note on materials	RoHS compliant
Mounting material	high-alloy stainless steel
Material of bearing	Polymer