

# Twin cylinder DPZJ-10-50-P-A-KF-S2

Part number: 162019

FESTO



 General operating condition

## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 50 mm  |
| Adjustable end position range/length     | 10 mm  |
| Piston diameter                          | 10 mm  |
| Drive unit operating mode                | Yoke   |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Guide                                    | Recirculating ball bearing   |
| Structural design                        | Guide  |
| Position sensing                         | Via proximity switch   |
| Symbol                                   | 00991243   |
| Variants                                 | Through piston rod   |
| Operating pressure                       | 0.25 MPa ... 1 MPa   |
| Operating pressure                       | 2.5 bar ... 10 bar   |
| Max. speed                               | 1 m/s  |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 0 - No corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C ... 80 °C   |
| Impact energy in the end positions       | 0.08 J   |
| Theoretical force at 6 bar, retracting   | 60 N   |
| Theoretical force at 6 bar, advancing    | 60 N   |
| Alternative connections                  | See product drawing  |
| Pneumatic connection                     | M5   |
| Cover material                           | Wrought aluminum alloy   |
| Seals material                           | NBR  |
| Housing material                         | Wrought aluminum alloy   |
| Piston rod material                      | Case-hardened steel  |