

Pressure regulator LR-1-D-O-MAXI

Part number: 162597

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Maxi |
| Series | D |
| Actuator lock | Rotary knob with detent |
| Mounting position | Any |
| Structural design | Pilot-controlled piston control valve |
| Controller function | Constant output pressure With secondary exhausting |
| Symbol | 00991559 |
| Pressure gauge | Set up for G1/4 |
| Operating pressure | 0 MPa ... 1.6 MPa |
| Operating pressure | 0 bar ... 16 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.04 MPa |
| Max. pressure hysteresis | 0.4 bar |
| Max. pressure hysteresis | 5.8 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 11500 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 700 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G1 |
| Pneumatic connection 2 | G1 |
| Note on materials | RoHS compliant |
| Material of sub-base | Die-cast zinc |
| Seals material | NBR |
| Housing material | Die-cast zinc |