


Vacuum generator VADM-200

Part number: 162504

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Nominal width of Laval nozzle	2 mm
Width dimension	22 mm
Muffler construction type	Closed
Mounting position	Any
Ejector characteristics	High vacuum
Grade of filtration	≤40 µm
Manual override	Non-detenting
Integrated function	Electric on-off valve Filter
Symbol	00991303
Valve function	Closed
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Operating pressure	29 psi ... 116 psi
Max. vacuum	85 %
Nominal operating pressure	0.6 MPa
Nominal operating pressure	6 bar
Nominal operating pressure	87 psi
Air supply time at nominal operating pressure	0.29 s
DC operating voltage range	21.6 V ... 26.4 V
Duty cycle	100%
Certification	c UL us - recognized (OL)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C ... 60 °C
Degree of protection	IP65
Ambient temperature	0 °C ... 60 °C
Product weight	320 g
Electrical connection	Plug
Type of mounting	With through-hole With internal thread
Pneumatic connection 1	G1/4

Feature	Value
Pneumatic connection 3	Integrated muffler
Vacuum connection	G3/8
Note on materials	RoHS compliant
Seals material	NBR
Female nozzle material	Brass, nickel-plated
Compressed air filter material	PA
Material of filter housing	PC
Housing material	Wrought aluminum alloy
Muffler material	Protective grounding POM
Material of piston	POM
Material of jet nozzle	Brass, nickel-plated