


Fine filter LFMB-3/8-D-MIDI

Part number: 162629

FESTO



 General operating condition

Data sheet

Feature	Value
Series	D
Size	Midi
Structural design	Fiber filter
Grade of filtration	1 µm
Condensate drain	Manual, rotating
Symbol	00991519
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:7:3] Inert gases
Max. standard flow rate for air quality class	1420 l/min
Min. standard flow rate for air quality class	500 l/min
Filter efficiency	99.99 %
Max. condensate volume	43 ml
Bowl guard	Metal bowl guard
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	1.5 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Storage temperature	-10 °C ... 60 °C
Residual oil content	0.5 mg/m ³
Type of mounting	With accessories
Mounting position	Vertical ±5°
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Housing material	Die-cast zinc
Compressed air filter material	Borosilicate glass fiber
Material of bowl	PC
Note on materials	RoHS compliant
Product weight	650 g