

ISO cylinder DNC-80-250-PPV

Part number: 163455

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 250 mm |
| Piston diameter | 80 mm |
| Piston rod thread | M20x1.5 |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 15552 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Profile barrel |
| Position sensing | None |
| Symbol | 00991232 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1.2 MPa |
| Operating pressure | 0.6 bar ... 12 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.9 J |
| Cushioning length | 32 mm |
| Theoretical force at 6 bar, retracting | 2721 N |
| Theoretical force at 6 bar, advancing | 3016 N |
| Moving mass at 0 mm stroke | 1131 g |
| Additional moving mass per 10 mm stroke | 38 g |
| Basic weight with 0 mm stroke | 2790 g |
| Additional weight per 10 mm stroke | 106 g |
| Type of mounting | With internal thread With accessories |
| Pneumatic connection | G3/8 |
| Note on materials | RoHS compliant |
| Cover material | Die-cast aluminum Coated |
| Seals material | TPE-U(PU) |

| Feature | Value |
|-----------------------------|---|
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | Wrought aluminum alloy Smooth-anodized |