

ISO cylinder DNC-125-100-PPV-A

Part number: 163501

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|--|
| Stroke | 100 mm |
| Piston diameter | 125 mm |
| Piston rod thread | M27x2 |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mounting position | Any |
| Conforms to standard | ISO 15552 |
| Piston rod end | External thread |
| Structural design | Piston Piston rod Profile barrel |
| Position sensing | For proximity sensor |
| Symbol | 00991235 |
| Variants | Piston rod at one end |
| Operating pressure | 0.06 MPa ... 1 MPa |
| Operating pressure | 0.6 bar ... 10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 5 J |
| Cushioning length | 42 mm |
| Theoretical force at 6 bar, retracting | 6881 N |
| Theoretical force at 6 bar, advancing | 7363 N |
| Moving mass at 0 mm stroke | 2809 g |
| Additional moving mass per 10 mm stroke | 63 g |
| Basic weight with 0 mm stroke | 6771 g |
| Additional weight per 10 mm stroke | 168 g |
| Type of mounting | With internal thread With accessories |
| Pneumatic connection | G1/2 |
| Note on materials | RoHS-compliant |
| Cover material | Die-cast aluminum Coated |
| Seals material | TPE-U(PU) |

| Feature | Value |
|-----------------------------|------------------------|
| Piston rod material | High-alloy steel |
| Material of cylinder barrel | Wrought aluminum alloy |
| | Smooth anodized |