

Mini slide SLS-10-15-P-A

Part number: 170493

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Stroke | 15 mm |
| Piston diameter | 10 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Guide | Ball bearing cage guide |
| Structural design | Yoke Piston Piston rod Ball cage guide Slide |
| Position sensing | Via proximity switch |
| Symbol | 00991737 |
| Operating pressure | 0.1 MPa ... 1 MPa |
| Operating pressure | 1 bar ... 10 bar |
| Operating pressure | 14.5 psi ... 145 psi |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -20 °C ... 60 °C |
| Impact energy in the end positions | 0.05 J |
| Max. force F _y | 170 N |
| Max. force F _z | 170 N |
| Max. torque M _x | 1.1 Nm |
| Max. torque M _y | 1.1 Nm |
| Max. torque M _z | 0.7 Nm |
| Theoretical force at 6 bar, retracting | 39 N |
| Theoretical force at 6 bar, advancing | 47 N |
| Moving mass | 49 g |
| Product weight | 149 g |
| Alternative connections | See product drawing |
| Type of mounting | With through-hole |
| Pneumatic connection | M5 |
| Note on materials | RoHS compliant |
| Cover material | Wrought aluminum alloy, anodized |

| Feature | Value |
|------------------|----------------------------|
| Guide material | Steel |
| Housing material | high-alloy stainless steel |