

Guided drive DFM-12-40-P-A-GF

Part number: 170828

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Distance of centre of gravity of payload to yoke plate xs | 25 mm |
| Stroke | 40 mm |
| Piston diameter | 12 mm |
| Drive unit operating mode | Yoke |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Guide | Plain-bearing guide |
| Structural design | Guide |
| Position sensing | Via proximity switch |
| Symbol | 00991737 |
| Operating pressure | 0.2 MPa ... 1 MPa |
| Operating pressure | 2 bar ... 10 bar |
| Max. speed | 0.8 m/s |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in the end positions | 0.07 J |
| Max. force Fy | 240 N |
| Max. force Fy static | 240 N |
| Max. force Fz | 240 N |
| Max. force Fz static | 240 N |
| Max. torque Mx | 4.92 Nm |
| Max. static moment Mx | 4.92 Nm |
| Max. torque My | 3.74 Nm |
| Max. static moment My | 3.74 Nm |
| Max. torque Mz | 3.74 Nm |
| Max. static moment Mz | 3.74 Nm |
| Max. permissible torque load Mx as a function of the stroke | 0.81 Nm |
| Max. payload as a function of the stroke at defined distance xs | 31 N |
| Theoretical force at 6 bar, retracting | 51 N |
| Theoretical force at 6 bar, advancing | 68 N |
| Moving mass | 232 g |

| Feature | Value |
|-------------------------|----------------------------|
| Product weight | 497 g |
| Alternative connections | See product drawing |
| Pneumatic connection | M5 |
| Note on materials | RoHS compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | NBR |
| Housing material | Wrought aluminum alloy |
| Piston rod material | high-alloy stainless steel |