

# Guided drive DFM-16-40-P-A-GF

Part number: 170836

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	50 mm
Stroke	40 mm
Piston diameter	16 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Plain-bearing guide
Structural design	Guide
Position sensing	Via proximity switch
Symbol	00991737
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in the end positions	0.15 J
Max. force Fy	608 N
Max. force Fy static	608 N
Max. force Fz	608 N
Max. force Fz static	608 N
Max. torque Mx	13.98 Nm
Max. static moment Mx	13.98 Nm
Max. torque My	10.34 Nm
Max. static moment My	10.34 Nm
Max. torque Mz	10.34 Nm
Max. static moment Mz	10.34 Nm
Max. permissible torque load Mx as a function of the stroke	2.44 Nm
Max. payload as a function of the stroke at defined distance xs	73 N
Theoretical force at 6 bar, retracting	90 N
Theoretical force at 6 bar, advancing	121 N
Moving mass	343 g

<b>Feature</b>	<b>Value</b>
Product weight	710 g
Alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	high-alloy stainless steel