

On/off valve HEE-1/2-D-MIDI-24

Part number: 172944

FESTO



General operating condition

Data sheet

Feature	Value
Structural design	Piston gate valve
Actuation type	Electrical
Sealing principle	Soft
Exhaust air function	Cannot be throttled
Manual override	Detenting
Reset method	Mechanical spring
Type of control	Piloted
Symbol	00991008
Valve function	3/2-way, closed, monostable
Operating pressure	0.25 MPa ... 1.6 MPa
Operating pressure	2.5 bar ... 16 bar
Lap	Positive overlap
C value	17 l/sbar
b-value	0.3
Normal nominal flow rate (normalized to DIN 1343)	3600 l/min
Duty cycle	100%
Coil characteristics	24 V DC: 2.5 W
Permissible voltage fluctuations	+/- 10%
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Type of mounting	In-line installation With accessories
Mounting position	Any
Flow direction	Non-reversible
Product weight	500 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Pneumatic connection 3	G1/4
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gases

Feature	Value
Electrical connection	Type C Plug As per DIN EN 175301-803
Signal status display	With accessories
Seals material	NBR
Housing material	Die-cast aluminum