

Filter regulator LFR-3/8-D-MIDI-NPT

Part number: 173780

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Midi |
| Series | D |
| Grade of filtration | 40 µm |
| Condensate drain | Manual, non-detenting |
| Max. condensate volume | 43 ml |
| Bowl guard | Metal bowl guard |
| Symbol | 00991585 |
| Operating pressure | 0.1 MPa ... 1.6 MPa |
| Operating pressure | 1 bar ... 16 bar |
| Max. pressure hysteresis | 0.2 bar |
| Normal nominal flow rate (normalized to DIN 1343) | 3100 l/min |
| Operating medium | Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 920 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 2 | 3/8 NPT |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |